

COPSIL 2

COPSIL 2 is a technical silicone elastomer with high mechanical properties. It can be used in contact with the skin as it complies with the ISO 10993-5 standard.

COPSIL 2 is made of a two-component system (resin & hardener) to be mixed in equal parts. It crosslinks at room temperature by polyaddition reaction thanks to a platinum complex based catalyst. The polymerization can be accelerated by heat.

Easy to use thanks to a satisfying fluidity and its simple ratio mix, it is aimed to the manufacture of low hardness parts (2-3 ShA or 33 Sh00).

Mixing of the components

The weighing of the components must be done in the same container, one after another. The mixing ratio must be respected as precisely as possible.

This system can be implemented either manually, or with a mechanical mixer at low speed (less than 300 rpm) to avoid the incorporation of air bubbles. It is then advised to degas the mix thanks to a vacuum pump.

A two-component casting machine must be used in accordance with the ratio mix.

Casting and reactivity

The crosslinking reaction for polyaddition silicones catalyzed with platinum complex can be inhibited by contact with certain materials, i.e. products with natural rubber vulcanized with Sulphur (DO NOT use latex gloves, only vinyl gloves), from chlorine, from certain synthetic rubbers, from certain polycondensation silicones catalyzed with tin salts, from certain plasticizers, from amines used as hardener in epoxy resins, plastiline, etc...

This list is not exhaustive, and we always advise a trial run.

The mechanical characteristics of the COPSIL 2 are stable after 24 hours. These times can be considerably reduced by placing the mold in an oven. The temperature not to be exceeded is 135°C.



Characteristics of the polymerized product

Hardness Shore A: 2

Hardness Shore 00: 33

Maximum elongation in %:

on unnotched rings: 500

on notched rings: 430

Maximum resistance in N/mm²:

on unnotched rings: 1

on notched rings: 0.7

Characteristics of the liquid product

Aspect:

Transparent, lightly translucent for both the resin and the hardener.

Density:

Approx. 1 for the two components.

Viscosity at 20°C in mPa.s:

- Approx. 4 000: NORMAL resin
- Approx. 8 000: NORMAL hardener
- Approx. 3 500: FAST resin
- Approx. 6 500: FAST hardener

Mixing ratio in weight:

Resin 100 parts

Hardener 100 parts

TIME	NORMAL	FAST
Working time at 20 °C	50 min	20 min
Demolding time at 20 °C	3 h 30	1 h 30

Packaging

The COPSIL 2 is available in 500 g pots, as well as in 5 kg and 25 kg buckets and in 2x200 mL cartridges. Here are their references:

NAMES	PACKAGING	REFERENCE
COPSIL 2 NORMAL	KIT 1 KG (500 g + 500 g)	T-02SN 01
	KIT 10 KG (5 kg + 5 kg)	T-02SN 10
	KIT 50 KG (25 kg + 25 kg)	T-02SN 50
COPSIL 2 FAST	KIT 1 KG (500 g + 500 g)	T-02SR 01
	KIT 10 KG (5 kg + 5 kg)	T-02SR 10
	KIT 50 KG (25 kg + 25 kg)	T-02SR 50
	CARTRIDGES (2 x 200 ml)	T-02SR C400

Storage, handling and safety

In its original packaging, the silicone elastomer COPSIL 2 is guaranteed 12 months if both components are stored away from light, humidity, well closed and at a room temperature below 30°C.

Rather use these products as soon as they are open. Usual health and safety conditions must be applied during the handling of the COPSIL 2. To do so, please read carefully our H&S Data Sheet, as well as the information given on the product's label.

Information contained in this document is supplied in good faith and based on our current knowledge. It is for indication and not formal constraint, in particular if this product is not used according to the applications expressed in this technical index card. A preliminary test will always be advised to be sure that the product corresponds to the customer's requirements.

The user of this product undertakes to respect the current legislation for the elimination of waste.

Customs' code

COPSIL 2 resin & hardener

39100000